



Siemens Technical Bulletin STAB15-0094

New Default Channels for WiMag Repeaters

27th April 2015

Product: *WiMag*

Modifications Req: *No*

Retrospective Action Req: *No*

Priority of Change: *Information Only*

- ✓ Introduction
- ✓ Scope
- ✓ Procedure
- ✓ Related documents

Introduction

This Bulletin provides notification that the default channels are changing in future shipments of WiMag Repeaters.

Scope

WiMag Repeaters.

Procedure

Starting in April, the WiMag repeaters shipped to Siemens will have default RF channels of **4 upstream** and **5 downstream**, rather than the current 0 and 1.

This is to avoid some field problems, related to the possibility of Repeaters locking to the wrong Access Point when kitting is not done at the office and installations have multiple Access Points.

All quick start guides and installation guides will be edited to reflect the change and these will be included in the shipments.

The shipment detail sheets will also reflect the new default channels and a new sticker will be added on all new repeater battery pack bags indicating the channels defaults.

Please take care if using these new repeaters with an previously installed base, as the defaults channels may need to be changed to match the existing equipment.

Related documents

667/HB/47200/000 - WiMag Vehicle Detection System General Handbook

Approved by: Priscilla Boyd

Harry Smyth

Senior Product Engineer

Technical Support

Traffic Solutions

Sopers Lane, Poole, Dorset BH17 7ER

Tel: +44 (0)1202 782027

Email: > harry.smyth@siemens.com

> www.siemens.co.uk/traffic

Committed to quality traffic solutions and service excellence